




Oxoeicosanoid Receptor 1 Antibody

CATALOG NUMBER: 48-155



Immunohistochemistry staining of Oxoeicosanoid receptor 1 in liver tissue using Oxoeicosanoid receptor 1 Antibody.

Specifications	
SPECIES REACTIVITY:	Gorilla, Human
TESTED APPLICATIONS:	IHC
APPLICATIONS:	Oxoeicosanoid Receptor 1 antibody can be used in ELISA, Western Blot, and immunohistochemistry starting at 5 ug/mL.
USER NOTE:	Optimal dilutions for each application to be determined by the researcher.
SPECIFICITY:	BLAST analysis of the peptide immunogen showed no homology with other human proteins.
IMMUNOGEN:	Oxoeicosanoid Receptor 1 antibody was raised against a peptide located in the 1st extracellular domain of Oxoeicosanoid Receptor 1 (Human).
HOST SPECIES:	Rabbit
Properties	
PURIFICATION:	Immunoaffinity Chromatography
PHYSICAL STATE:	Liquid
BUFFER:	PBS, 0.1% sodium azide.
STORAGE CONDITIONS:	Oxoeicosanoid Receptor 1 antibody should be stored long term (months) at -80 °C and short term (days) at 4 °C. As with all antibodies avoid freeze/thaw cycles.
CLONALITY:	Polyclonal
CONJUGATE:	Unconjugated
Additional Info	
ALTERNATE NAMES:	OXER1, GPR170, G-protein coupled receptor 170, HEOAD54, Oxoeicosanoid (OXE) receptor 1, Oxoeicosanoid receptor 1, TG1019
ACCESSION NO.:	Q8TDS5
PROTEIN GI NO.:	74762623
OFFICIAL SYMBOL:	OXER1
GENE ID:	165140

Background

BACKGROUND: OXER1 is a Chemoattractant Receptor for eosinophils and neutrophils.

FOR RESEARCH USE ONLY

December 13, 2016